



*Commercial, Industrial  
and Residential Electrical Products*

## NEMA 1 Dugout Transition Box with STAB-IT® Cable Clamps, 8X20X6

Catalog #:  
SC082006STRC



### FEATURE BENEFIT

RACO's Dugout box offers the quickest and easiest way to transition from flexible armored cable to conduit before entering the circuit panel. The Dugout box offers more labor savings and installation flexibility than any other transition box on the market.

### PRODUCT FEATURES

- Includes 21 STAB-iT connectors to hold up to 42 MC cables
- Designed for quick installation of flex, MC, MCI, MCI-A, AC and HCF cable
- STAB-iT® clamp has been tested at over 3X's faster than traditional MC connectors
- Room to add up to six additional STAB-iT® connectors
- Accepts cable sizes from 14/2 up to 10/3 for most cable types
- Features (4) 3/4 - 1 In. Concentric Knockouts
- Covered included
- Designed and assembled in the USA

### APPLICATIONS

RACO's Dugout box offers the quickest and easiest way to transition from flexible armored cable to conduit before entering the circuit panel. Specifically designed for commercial applications, the Dugout box builds on the popular concept of our Grand Slam box. This roomy rectangular model features plenty of space for wiring along with 21 of our built-in STAB-iT cable clamps, which hold up to 42 MC cables! Our unique clamps are field-proven to install up to 3X faster than traditional MC connectors. Four concentric knockouts are provided for either 3/4 In. or 1 In. conduit out to the circuit panel. For wall or ceiling mounting. The Dugout box offers more labor savings and installation flexibility than any other transition box on the market. Specifically designed for commercial applications, the Dugout box builds on the popular concept of our Grand Slam box. This roomy rectangular model features plenty of space for wiring along with 21 of our built-in STAB-iT cable clamps, which hold up to 42 MC cables! For wall or ceiling mounting.

### CERTIFICATIONS



### PRODUCT SPECIFICATIONS

UPC Number:	050169995655
Ea Length/Depth (in.):	6.272
Ea Width (in.):	20.375
Ea Height (in.):	8.125
Wt. Ea. (Lbs.):	13.95
Package Type:	Loose
Product UPC-A Labeled:	Yes

### PACKAGING

Case 12of5:	50050169995650
Standard Carton Qty:	1
Min Order Qty:	1



▲ WARNING: Cancer and Reproductive  
Harm - www.P65Warnings.ca.gov.

Revision 1, July 2020



**COMMERCIAL  
CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

**RACO**  
3902 W. Sample St.  
South Bend, IN 46619  
574-234-7151  
[www.hubbell.com/raco/en](http://www.hubbell.com/raco/en)

