



1-Gang Weatherproof In-Use Cover, EXTRA DUTY®, Expandable, Vertical, 8-in-1, 3-1/2 in. Deep, Bronze

By TayMac
Catalog # [MX4280Z](#)



1-Gang Weatherproof In-Use Cover, EXTRA DUTY®, Expandable, Vertical, 8-in-1, 3-1/2 in. Deep, Bronze

Features

- Revolutionary patented design expands from 1 in. to 3-1/2 in. for in-use needs
- Heavy duty die-cast metal construction with premium powder coat
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 8-in-1 custom device configurations, comes pre-configured for GFCI
- Lockable open or closed and fits fullsize padlock
- Adapter, gasket, mounting hardware and instructions included
- Extra Duty® rated
- Vertical mount

General

Application	In Use
Catalog Number	MX4280Z
Color	Bronze
Construction	Metallic
Cover Type	In-Use;Low Profile
EU RoHS Indicator	Contact Manufacturer
Mounting Method	Vertical
Number of Gang(s)	1-Gang
Type	Cover
UPC	092326117395

Dimensions

Actual Depth	2.25 in
Cubic Capacity	76.2125 cu.in
Depth	3.5 in
Height	6.5 in
Weight	0.8 lb
Width	3.35 in

Certifications And Compliance

Certified Listed Compliance	UL Listed Extra-Duty Compliant
NEC Nema Rating	Compliant NEMA 3R

Logistics

Carton Quantity	6
Packaging Type	Shrink
Pallet Quantity	1080
Standard Package	6

Product Assets

- [Brochures - TayMac Extra Duty In-use Covers](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Product Logo - ExtraDuty](#)
- [Sales Drawings - MX4280S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TAYMAC: Metallic Extra Duty Weatherproof In-Use Device Covers](#)
- [Video - TAYMAC: Extra-Duty Overview](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-MX4280Z-SPEC-EN | REV 6/2024