

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex, Heavy Duty  
Grade, 2-Pole 3-Wire Grounding,  
20A 250V, 6-20R, White**

By Hubbell Wiring Device-Kellems  
Catalog # [5462WHI](#)

Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade,  
2-Pole 3-Wire Grounding, 20A 250V, 6-20R, White



## General

Application	Hubbell-Pro Heavy Duty
Catalog Number	5462WHI
Color	White
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V-2
	Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Hubbell-PRO
Style	Smooth Face
Type	Standard Duplex
	Standard Duplex
UPC	783585555928

## Dimensions

Weight	0.2 lb
--------	--------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating Description	250 V
Wattage	5000 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA 22.2, No. 42
	Fed. Spec. W-C-596
	NEMA® WD-6 Compliant
	UL Listed to UL498 File No. E2186
Nema Rating	6-20R

## Logistics

Carton Quantity	10
Pallet Quantity	5000

## Product Assets

[Catalog Page - WDK A-28 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - 5462WHI AutoCAD Drawing](#)  
[Literature - Hubbell-PRO 15A & 20A 250V Duplex Receptacles](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-5462WHI-SPEC-EN | REV 6/2024