

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A and 100A 1 1/2" NPT Hub, 4 Way Angled, Mounting Screws Included

By Hubbell Wiring Device-Kellems
Catalog # [FW60100](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade, Accessory, Back Box, for 60A and 100A 1½" NPT Hub, Four Way Angled, Mounting Screws Included

Features

- Industrial Grade
- Back Box
- For 60A and 100A 1 1/2" NPT Hub

Application

Metallic

General

Catalog Number	FW60100
Construction	Cast
EU RoHS Indicator	No
Item Type	Mounting Box
Knockouts	1 1/2" NPT Hub
Material	Aluminum
Material - Mounting Hardware	Mounting Screws
Number Of Outlets	Accepts 1-Device
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Back Boxes and Adapters
Specifications	<ul style="list-style-type: none">• Accessory Item - Cast Aluminum Back Box• Back Box - Four Way 15 Degree A• Box Hub Size - 1 1/2" NPT
Style	15 Degree
Temperature Range	Limited By Device
Type	Back Box
UPC	783585750262

Dimensions



Display Size	For 60, 63, 100 and 125A Devices
--------------	----------------------------------

Conductor Related

Cable Entry	Through Hub
-------------	-------------

Certifications And Compliance

Industry Standard(s)	UL Raintight and External Icing Test
----------------------	--------------------------------------

Logistics

Carton Quantity	1
Pallet Quantity	100

Product Assets

- [Catalog Page - WDK AA-21](#)
- [Catalog Page - WDK G-28](#)
- [Catalog Page - WDK AA-20](#)
- [Catalog Page - WDK H-13](#)
- [Catalog Page - WDK G-35](#)
- [Catalog Page - WDK AA-24](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Sales Drawings - WDK_FW60100_DRAWING_PDF](#)
- [Specifications - Wiring FW60100 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)