



6-Gang CFB Series Box for Round Covers, 3/4" Stackable Rings, Prepour Installation

By Hubbell Wiring Device-Kellems
Catalog # [CFB6RCVRR075](#)



Concrete Floorboxes, Recessed, 6-Gang CFB Series Box for Round Covers, 3/4" Stackable Rings, Prepour Installation

Features

- CFB2G Series Concrete Round Cover Floorbox Pre-pour Stackable Ring
- Increases Box Height by 3/4" Increments
- MUST BE INSTALLED BEFORE CONCRETE POUR

Application

For Use with Concrete Floor Boxes

General

Accessory Type	Adjustment Rings
Application - For Use On	Concrete
Color	Metallic
Construction	Fabricated
Cover Shape	Rectangle; Round
Cover Type	Rectangle; Round
EU RoHS Indicator	Contact Manufacturer
Material	Pre Galvanized Steel
Mounting Method	Cast Into Concrete
Mounting Type	Screw Mount
Number of Gang(s)	2-Gang
Series	Recessed - CFB Series
Size	2-Gang;4-Gang;6-Gang;10-Gang
Sub Brand	Recessed Concrete Floor Boxes
Type	Prepour Stackable Ring
UPC	783585546018

Conductor Related

Cable Entry Through Cover

Certifications and Compliance

Industry Standard(s) cULus

Logistics

Carton Quantity 10

Product Assets

[Engineering Drawing - CFB6RCVRR075 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2751_INSTALLINST](#)
[Literature - Hubbell SystemOne Recessed Floor Boxes](#)
[Sales Drawings - WDK_CFB6RCVRR075_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - SystemOne Recessed Floor Boxes](#)

Related Products

[CFB2G25R - 2-Gang CFB Series Box for Round Covers, 3.25" Minimum Depth of Pour](#)
[CFB2G30R - 2-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour](#)
[CFB2G30RCR - 2-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour, Corrosion Resistant Paint](#)
[CFB2G25RCR - 2-Gang CFB Series Box for Round Covers, 3.25" Minimum Depth of Pour, Corrosion Resistant Paint](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-CFB6RCVRR075-SPEC-EN | REV 5/2023