

**HUBBELL**  
Wiring Device-Kellems

## **Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Automatic Set, 30A, 240V AC, 50', Yellow**

By Hubbell Wiring Device-Kellems  
Catalog # [GFP2311](#)

Power Protection Products, GFCI High Amperage Portables,  
Industrial/Commercial, Auto Set, 30A 240V AC, 2' Cord Length,  
4-6 mA Trip Level, Yellow.



## General

Application	Line Cord Only No Devices
Catalog Number	GFP2311
Color	Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure  Electrical - Operating Voltage Range - 85% to 110%  Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC  Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency  Environmental - Construction - Industrial grade design  Environmental - Housing Rating - UL Type 4X  Environmental - Leakage Current - At 93% Humidity leakage current is zero  Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F.  Environmental - Type - Meets UL943 Class A GFCI

Series	Extra Heavy Duty
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Straight Blade
UPC	783585005638

## Dimensions

Outside Diameter	0.335
Weight	2.15 lb

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	240 VAC
Voltage Rating Description	240 VAC

## Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD1827\\_INSTALLINST](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_GFP23\\_DRAWINGS\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-GFP2311-SPEC-EN | REV 6/2024