




Wiring Device-Kellems

Power Protection Products, GFCI Receptacle, Duplex, SNAP-Connect, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, USA

By Hubbell Wiring Device-Kellems
Catalog # [GFRST15SNAPLANA](#)



Power Protection Products, GFCI Receptacle, Duplex, SNAP-Connect, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond, USA

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Color	Light Almond
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Assembled In USA
Type	Standard
UPC	883778430558

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity 10

Product Assets

[Engineering Drawing - GFRST15SNAPLANA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2484_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_GFRST15SNAPNA_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[GFRST15LA - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 15A, Light Almond](#)
[GFRST20LANL - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle with Nightlight, 20A, Light Almond](#)
[GFRST20LA - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 20A, Light Almond](#)
[GFTRST20LANL - Heavy Duty Commercial Tamper-Resistant AUTOGUARD® Self-Test GFCI Receptacle with Nightlight, 20A, Light Almond](#)
[GFBFST20LA - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI with Blank Face, 20A, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-GFRST15SNAPLANA-SPEC-EN | REV 5/2023