

PS, IEC, PLUG, 2P3W,100A 550V DC  
ONLY,VX

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3100P8V0DC](#)

PS, IEC, PLUG, 2P3W,100A 550V DC ONLY,VX

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Raised collar surrounds each phase pin

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL3100P8V0DC
Color	Black
Number Of Poles	2-Pole
Series	DC Rated
Specifications	<ul style="list-style-type: none"><li>• Cord Clamp - Reinforced Thermoplastic Polyester</li><li>• Gland - Solid Neoprene</li><li>• Housing - Valox®</li><li>• Locking Ring - Reinforced Thermoplastic Polyester</li></ul>



Style	Sealing Gasket - Solid Neoprene
Type	Standard Service Watertight Plug
UPC	783585242293

Electrical Ratings

Amperage Rating	100 A
Current / Amperage Rating	100 A
Voltage Rating	550 VDC
Voltage Rating Description	550 VDC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified File LR280C</li><li>• UL Classified to IEC 60309-1 IEC 60309-2</li><li>• UL Listed, File E146033</li></ul>
----------------------	--

Logistics

Carton Quantity	6
-----------------	---

Product Assets

- [Catalog Page - WDK G-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL3100P8V0DC AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2388\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL3100P\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL3100P8V0DC Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)

