



Surge Protective Devices, Hospital Grade Outlet Strip, 20A 125V, 6' Cord Length

By Hubbell Wiring Device-Kellems
Catalog # [HBL6HG620](#)



Surge Protective Devices, Hospital Grade Outlet Strip, 20A 125V, 6' Cord Length

Features

- Hospital grade tamper-resistant receptacles with a hospital grade plug
- cULus 1449 4th edition
- Heavy duty metal housing
- Available with a 2-port USB charging outlet

General

Color	White
EU RoHS Indicator	Contact Manufacturer
Number Of Outlets	6
Series	Healthcare
Type	Metallic
UPC	783585467849

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Wiring M16 Catalog page](#)
[Catalog Page - Wiring N-9 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - HBL6HG620 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2699_INSTALLINST](#)
[Literature - Hubbell Power Strips](#)
[Literature - Healthcare Product Solutions](#)
[Literature - WLBD026_Duct Products Brochure_WEB](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL6HG_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)

Related Products

[SNAP8362S - Straight Blade Devices, Decorator Duplex Receptacle, Hospital Grade, SNAP-Connect, Surge suppression, Tamper Resistant, LED Indicator, 20A 125V](#)
[HBL8362SA - Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, Duplex, 20A 125V, 5-20R, Blue](#)
[HBL6HG1520 - Surge Protective Devices, Hospital Grade Outlet Strip, 20A 125V, 15' Cord Length](#)
[IG8362SA - Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Red](#)
[HBL6HG15 - Surge Protective Devices, Hospital Grade Outlet Strip, 15A 125V, 15' Cord Length](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL6HG620-SPEC-EN | REV 5/2023