



# Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White



By Hubbell Wiring Device-Kellems  
Catalog # [HBL6PS35015A](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White

## Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

## Application

6 Outlet, Standard Devices

## General

Color	<ul style="list-style-type: none"> <li>• Office White</li> <li>• Blanc cassé</li> </ul>
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> <li>• Electrical - Max Surge Current - 6.5kA</li> <li>• Electrical - Max. Operating Voltage - 130</li> <li>• Electrical - Operating Frequency - 50/60Hz</li> <li>• Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)</li> </ul>
Response Time	5
Series	Economy Surge Strips
Type	Non-Metallic
UPC	783585120522

## Dimensions

Display Size 350 Joules

## Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

## Conductor Related

Cord Length 15 ft

## Logistics

Carton Quantity 12

## Product Assets

[Catalog Page - Wiring N-9 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - HBL6PS35015A AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2380\\_INSTALLINST](#)  
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)  
[Sales Drawings - WDK\\_HBL6PS350\\_DRAWING\\_PDF](#)  
[Warranty - Surge Plug Strips](#)

## Related Products

[HBL7PS1050A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White](#)  
[HBL4PS1050USBA - Surge Protective Devices, SPIKESHIELDTVSS Plug Strips, 4 Outlet, 2.4A USB, 1050 Joules, 6' Cord, Black](#)  
[HBL6PS1050MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet with Telephone/Fax, 6' Cord, Office White](#)  
[HBL7PS105015A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 15' Cord, Office White](#)  
[HBL7PS1050MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office White](#)



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBL6PS35015A-SPEC-EN | REV 5/2023