

HUBBELL
Wiring Device-Kellems

Hospital Grade Surge Suppression Receptacle, Duplex, 15A 125V, 5- 15R, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL8262GYSA](#)

Hospital Grade Surge Suppression Receptacle, Duplex, 15A 125V,
5-15R, Gray



General

Application	Decorator Duplex with Light and Alarm
Catalog Number	HBL8262GYSA
Color	Gray
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	Electrical - Frequency - 60Hz Electrical - Protection Modes - Normal and Common Modes Electrical - Response Time - Approximately 5 ns Electrical - Transient Suppression - Peak Energy (10 X 100 Qs) Peak Current (8 X 20 Qs) Electrical - Voltage - 120V AC + 10% - 15% Environmental - Flammability - UL 94V-2 Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Hospital Grade
Type	Duplex Duplex
UPC	783585060354

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	CSA Certified to Specification C22.2 No. 42
	Listed to UL Standards 498 Receptacles
	UL Listed File E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK M-13 Catalog Page](#)
[Catalog Page - WDK L-16 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL8262GYSA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1152_INSTALLINST](#)
[Literature - Duct Products Guide](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL8262_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBL8262GYSA-SPEC-EN | REV 6/2024