



## Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [GFBFHP20GY](#)

Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Gray

### Features

- Blank face 1.5 horsepower motor control rated switch UL508 listed. Also listed to Underwriters Laboratories standard 943 for Class A GFCI
- If wired incorrectly there will be no power to the face or to downstream receptacles for added safety. (2) LED indicators provide immediate status of power, trip condition and ability to provide GFCI protection
- In addition to providing Class A GFCI protection, the HP series includes a 1.5 HP rating for motor control switching per UL508

### General

Color	<ul style="list-style-type: none"><li>• Gray</li><li>• Gris</li></ul>
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Blank Face, 1.5HP
Type	Standard
UPC	883778450037

### Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V



### Logistics

Carton Quantity 10

### Product Assets

[Catalog Page - Wiring L-8 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - GFBFHP20GY AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2082\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_GFBFHP20\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

### Related Products

[GFBFHP20R - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Red](#)  
[GFBFST20GY - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI with Blank Face, 20A, Gray](#)  
[GFBFHP20 - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Brown](#)  
[GFBFHP20W - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, White](#)  
[GFBFHP20I - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-GFBFHP20GY-SPEC-EN | REV 5/2023