

HUBBELL
Wiring Device-Kellems

Circuit Guard® Extra Heavy Duty Hard Wired GFCI with Automatic Set, 30A, 3Ø 120/208V AC, Yellow

By Hubbell Wiring Device-Kellems

Catalog # [GFHW431](#)

Power Protection Products, Hard Wired GFCI,
Industrial/Commercial, No Output, 30A 3-Phase 120/208V AC,
4-6 mA Trip Level, Yellow.



General

Application	Wire Into Circuit
Catalog Number	GFHW431
Color	Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Thermoplastic
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure Electrical - Operating Voltage Range - 85% to 110% Electrical - Rated Voltage - 120V AC, 240V AC & 120/240V, 3Ø 250V AC, 3Ø 120/208V AC Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency Environmental - Construction - Industrial grade design Environmental - Housing Rating - UL Type 4X Environmental - Leakage Current - At 93% Humidity leakage current is zero Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F. Environmental - Type - Class A GFCI
Series	Extra Heavy Duty
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Hard Wired
UPC	783585521091

Dimensions

Weight	2.4 lb
--------	--------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Hard Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase 120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	5
Strands	Multi

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK K-18 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFHW431 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1978_INSTALLINST](#)
[Literature - 20A & 30A GFCI Protected Cord Drops](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Safety Product Guide](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_GFHW431_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-GFW431-SPEC-EN | REV 6/2024