



# Power Protection Products, GFCI Receptacle, Duplex, SNAP-Connect, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, USA

By Hubbell Wiring Device-Kellems  
Catalog # [GFRST20SNAPWNA](#)



Power Protection Products, GFCI Receptacle, Duplex, SNAP-Connect, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, USA

## Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

## General

Color	White
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Assembled In USA
Type	Standard
UPC	883778430657

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity 10

## Product Assets

[Engineering Drawing - GFRST20SNAPWNA AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2484\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_GFRST20SNAPNA\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

## Related Products

[GFTRST20WNL - Heavy Duty Commercial Tamper-Resistant AUTOGUARD® Self-Test GFCI Receptacle with Nightlight, 20A, White](#)  
[GFRST20WNL - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle with Nightlight, 20A, White](#)  
[GFTRST20W - Heavy Duty Commercial Tamper-Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, White](#)  
[GFRST20SNAPW - SNAPConnect® Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 20A, White](#)  
[GFRST15WNL - Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle with Nightlight, 15A, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-GFRST20SNAPWNA-SPEC-EN | REV 5/2023