

Industrial Grade, 30 Amp Non-Fused Disconnect Switch, Three Pole, 600V AC, Screw Terminals, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3](#)



Switches and Lighting Controls, Industrial Grade, Non-fused Disconnect Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA4XEnclosure,

Application

- Labelless

General

Catalog Number	HBLDS3
EU RoHS Indicator	No
Horsepower - Maximum	15
Ingress Protection	IP69K
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	- Base - Valox® - Enclosure Gasket - Neoprene - Handle - Valox® - Shaft (Unfused) - Valox® - Top - Valox®
Style	Heavy Duty
Type	- Replacement Switches - Disconnect Switches - Accessories For LINKOSITY®
UPC	783585955001

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Weight	2.6 lb
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum
Phase	Three Phase

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Pallet Quantity	410

Product Assets

- [Catalog Page - WDK F-19 Catalog Page](#)
- [Catalog Page - WDK F-12 Catalog Page](#)
- [Catalog Page - WDK F-11 Catalog Page](#)
- [Catalog Page - WDK F-17 Catalog Page](#)
- [Catalog Page - WDK F-5 Catalog Page](#)
- [Catalog Page - WDK F-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLDS3 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1782_INSTALLINST](#)
- [Literature - Education Application Guide](#)
- [Literature - Food Processing Guide](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Industrial Solutions](#)
- [Literature - Labelless Disconnects](#)
- [Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_HBLDS3_DRAWING_PDF](#)
- [Specifications - Wiring HBLDS3 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLDS3-SPEC-EN | REV 7/2025