

Industrial Grade, Motor Disconnect,  
Unfused Switch, Non-Metallic  
Sloped Version Replacement Cover  
for 30A With inTOUCH Installation  
Free LED Phase Indication and Jog -  
HBLDS30 and HBLDS30T Series

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS30RCPJ](#)



Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic  
Sloped Replacement Sloped Cover for 30A HBLDS30 and  
HBLDS30T Series With inTOUCH Installation Free LED Phase  
Indication and Jog, cULus, NSF, CE, UL 508 / UL 60947-4-1A

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Certified by NSF for hygiene in food processing applications
- Product rating are permanently laser-marked and will not wash off
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

Application

Heavy Duty Industrial and/or Washdown

General

Catalog Number	HBLDS30RCPJ
Color	Gray
Enclosure Type	IP69k and UL Type 4X, 12
Environmental Conditions	Indoor and Outdoor
Ingress Protection	IP69k, NEMA Type 4X, 12
Material - Mounting Hardware	Stainless Steel Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum

Series Specifications	-40 °C
	Non-Fused
Style Type UPC	Enclosure Gasket - Neoprene
	Handle - Valox®
Replacement Cover Accessories	Shaft (Unfused) - Valox®
	Top - Valox®
783585763170	

Dimensions

Weight	1.1 lb
--------	--------

Certifications And Compliance

Industry Standard(s)	cULus Listed
----------------------	--------------

Product Assets

- [Brochures - Circuit-Lock® Motor Disconnects](#)
- [Catalog Page - WDK F-8 Catalog Page](#)
- [Installation Manuals - HUBBELL 30 AMP CIRCUIT-LOCK DISCONNECT SWITCH | Installation manual](#)
- [Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
- [Sales Drawings - M-14706](#)
- [Specifications - HBLDS30RCPJ](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)