



Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3AC2](#)

Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

Application

Labelless

General

EU RoHS Indicator	No
Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none">• Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage• Electrical - Dielectric Voltage - Withstands 3000V AC minimum• Electrical - Max. Working Voltage - 600V AC RMS• Environmental - Flammability - UL94-5VA and VO Classification• Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact• Environmental - UV Resistance - All materials are UV stabilized• Mechanical - Impact



Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1782_PD1789_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series	Non-Fused
Style	Heavy Duty
Type	Disconnect Switches
UPC	783585145440



A proud member of the Hubbell Family.