



Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 600V AC, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBSL460B5W](#)



Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 600V AC, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Color	Black
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Inlet
UPC	783585479262

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Product Assets

[Catalog Page - Wiring G-6 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - HBSL460B5W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBSL460B_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)

Related Products

[BB601W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/4" NPT Hub, Angled, Mounting Screws Included Cast Aluminum](#)
[HBSL460P5W - Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 3-Phase 600V AC, 3-Pole 4-Wire, NEMA 4X/IP 69K](#)
[PC60 - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic](#)
[BB602W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/2" NPT Hub, Angled, Mounting Screws Included Cast Aluminum](#)
[HBSL460R5W - Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA, With Pilot Contact 4X/IP69K](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBSL460B5W-SPEC-EN | REV 5/2023