

PS, IEC, CONN, 3P4W, 30A 380-415V, V0

By Hubbell Wiring Device-Kellems  
Catalog # [HBL430C6V02](#)

PS, IEC, CONN, 3P4W, 30A 380-415V, V0

Features

- Self-closing gasketed cover
- Color coded housings for easy identification
- Insulated non-metallic housing

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL430C6V02
Color	Red
Number Of Poles	3-Pole
Series	Dual Certified UL 1682 & TUV
Specifications	<ul style="list-style-type: none"><li>• Arm Springs - Stainless Steel</li><li>• Cord Clamps - Reinforced Thermoplastic Polyester</li><li>• Cover Arms - Reinforced Thermoplastic Polyester</li></ul>



Style  
Type  
UPC

- Glands - Solid Neoprene
  - Housing - Valox®
- Standard Service  
Watertight Connector Body  
783585155425

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Voltage Rating	380-415 VAC
Voltage Rating Description	380-415 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified File LR280C</li><li>• UL Classified to IEC 60309-1 IEC 60309-2</li><li>• UL Listed to UL1682</li></ul>
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL430C6V02 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1303\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL430C\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL430C6V02 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)