



Surge Protective Devices, Hospital Grade Outlet Strip, 15A 125V, 6' Cord Length

By Hubbell Wiring Device-Kellems
Catalog # [HBL6HG6](#)



Surge Protective Devices, Hospital Grade Outlet Strip, 15A 125V, 6' Cord Length

Features

- Hospital grade tamper-resistant receptacles with a hospital grade plug
- cULus 1449 4th edition
- Heavy duty metal housing
- Available with a 2-port USB charging outlet

General

Color	White
EU RoHS Indicator	Contact Manufacturer
Number Of Outlets	6
Series	Healthcare
Type	Metallic
UPC	783585467825

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - Wiring M16 Catalog page](#)
- [Catalog Page - Wiring N-9 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL6HG6 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2699_INSTALLINST](#)
- [Literature - Hubbell Power Strips](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL6HG_DRAWING_PDF](#)
- [Warranty - Surge Plug Strips](#)

Related Products

- [HBL6MG6 - Surge Protective Devices, Medical Grade Outlet Strip, 15A 125V, 6' Cord Length](#)
- [HBL6MGRPT15 - Power Strips, Medical Grade, 6\) Outlet, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 15' Cord](#)
- [HBL6MGRPT6 - Power Strips, Medical Grade, 6\) Outlet, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 6' Cord](#)
- [HBL8262SA - Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, Duplex, 15A 125V, 5-15R, Blue](#)
- [HBL6HGUSB6 - Surge Protective Devices, Hospital Grade Plug Strip, 6\) Receptacles, With USB Charger](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL6HG6-SPEC-EN | REV 5/2023