



# Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet with Telephone/Fax, 6' Cord, Office White



By Hubbell Wiring Device-Kellems  
Catalog # [HBL6PS1050MA](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet with Telephone/Fax, 6' Cord, Office White

## Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

## Application

6 Outlet, Standard Devices

## General

Color	Office White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> <li>• Electrical - Max Surge Current - 19.5kA</li> <li>• Electrical - Max. Operating Voltage - 130</li> <li>• Electrical - Operating Frequency - 50/60Hz</li> <li>• Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)</li> </ul>
Response Time	5
Series	Economy Surge Strips
Type	Non-Metallic
UPC	783585120546

## Dimensions

Display Size	1050 Joules
--------------	-------------

## Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

## Conductor Related

Cord Length	6 ft
-------------	------

## Logistics

Carton Quantity	12
-----------------	----

## Product Assets

- [Catalog Page - Wiring N-9 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL6PS1050MA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2380\\_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK\\_HBL6PS1050\\_DRAWING\\_PDF](#)
- [Warranty - Surge Plug Strips](#)

## Related Products

- [HBL7PS1050A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White](#)
- [HBL7PS1050MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office White](#)
- [HBL6PS35015A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White](#)
- [HBL6PS - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 6' Cord, Office White](#)
- [HBL8PS2100MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Fax, 2100 Joules, 6' Cord, Office White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBL6PS1050MA-SPEC-EN | REV 5/2023