



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL6PS350YL](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Yellow

Features

- Yellow color for high visibility and metal housing
- 350 joules, 6 foot cord, wire management

Application

Standard Devices and Cord Holder

General

| | |
|------------------------------|---|
| Color | <ul style="list-style-type: none"> • Yellow • Jaune |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Indicator(s) Type | LED Indicator |
| Item Type | Surge Protection Plug Strips |
| Material | Non-Metallic |
| Material - Mounting Hardware | Portable |
| Number Of Outlets | 6 |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Outlet | Straight Blade 5-15R |
| Performance | <ul style="list-style-type: none"> • Electrical - Max Surge Current - 6.5kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C) |
| Response Time | 5 |
| Series | Economy Surge Strips |
| Type | Metallic |
| UPC | 783585120607 |

Dimensions

Display Size 350 Joules

Electrical Ratings

| | |
|---------------------------|--------------|
| Connectivity | Plug-In |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Frequency Rating | 60 Hz |
| Phase | Single Phase |

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 12

Product Assets

[Catalog Page - Wiring N-9 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - HBL6PS350YL AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL6PS350YL_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)

Related Products

[HBL6PPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Plastic Body, 6' Cord, Office White](#)
[HBL6PS350A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Office White](#)
[HBL7PS1050A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White](#)
[HBL4PS1050USBA - Surge Protective Devices, SPIKESHIELDTVSS Plug Strips, 4 Outlet, 2.4A USB, 1050 Joules, 6' Cord, Black](#)
[HBL8PS2100MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Fax, 2100 Joules, 6' Cord, Office White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL6PS350YL-SPEC-EN | REV 5/2023