



Patch Cord, Speed Gain, Cat6, Slim, Blue, 5'

By Hubbell Wiring Device-Kellems
Catalog # [HC6B05](#)



Patch Cord, Speed Gain, Cat6, Slim, Blue, 5'

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

General

| | |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Attenuation | .1dB |
| Boot Type | PVC |
| Color | <ul style="list-style-type: none">• Blue• Bleu |
| EU RoHS Indicator | Yes |
| Item Type | NEXTSPEED Category 6 and 5e Patch Cords |
| Material - Insulation | Flame Redardant PVC |
| Material - Jacket | Flame Redardant PVC |
| Performance | <ul style="list-style-type: none">• Mechanical - Cable to plug tensile strength - 20+ lbs.• Mechanical - Mating Cycles - 2000+ |
| Plug Type | RJ45 |
| Temperature Rating | Per TIA |
| Type | Standard |
| UPC | 662620231501 |

Dimensions

| | |
|------------------|-------|
| Length | 5 ft |
| Outside Diameter | 0.218 |

Electrical Ratings

| | |
|----------------|------------|
| Voltage Rating | 300V AC kV |
|----------------|------------|

Conductor Related

| | |
|----------------------|-------------|
| Conductor Stranding | Stranded |
| Conductor Type | Copper |
| Number Of Conductors | 8-Conductor |
| Wire Size | #24 AWG |

Certifications and Compliance

| | |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6 Component• ISO 11801/60603-7-41 Category 6 Component |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC6B15 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 15'](#)
- [HC6B20 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 20'](#)
- [HC6B01 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 1'](#)
- [HC6B25 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 25'](#)
- [HC6Y05 - Patch Cord, Speed Gain, Cat6, Slim, Yellow, 5'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC6B05-SPEC-EN | REV 4/2023