



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 15' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL7PS105015A](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 15' Cord, Office White

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

Application

7 Outlet, Standard Devices

General

Color	Office White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	7
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> • Electrical - Max Surge Current - 19.5kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
Series	Economy Surge Strips
Type	Non-Metallic
UPC	783585120560

Dimensions

Display Size	1050 Joules
--------------	-------------

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	12
-----------------	----

Product Assets

- [Catalog Page - Wiring N-9 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL7PS105015A AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2380_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL7PS105015A_DRAWING_PDF](#)
- [Warranty - Surge Plug Strips](#)

Related Products

- [HBL4PS1050USBA - Surge Protective Devices, SPIKESHIELDTVSS Plug Strips, 4 Outlet, 2.4A USB, 1050 Joules, 6' Cord, Black](#)
- [HBL7PS1050A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White](#)
- [HBL7PS1050MA - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office White](#)
- [HBL6PS35015A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White](#)
- [HBL6PS350A - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Office White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL7PS105015A-SPEC-EN | REV 5/2023