

Industrial Grade, Motor Disconnect,
Unfused Switch, Non-Metallic
Sloped Version Replacement Cover
for 30A With inTOUCH Installation
Free LED Phase Indication -
HBLDS30 and HBLDS30T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30RCP](#)



Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic
Sloped Replacement Cover for 30A HBLDS30 and HBLDS30T
Series With inTOUCH Installation Free LED Phase Indication,
cULus, NSF, CE, UL 508 / UL 60947-4-1A

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

Application

Heavy Duty Industrial and/or Washdown

General

Catalog Number	HBLDS30RCP
Color	Gray
Enclosure Type	IP69k and UL Type 4X, 12
Environmental Conditions	Indoor and Outdoor
Ingress Protection	IP69k, NEMA Type 4X, 12
Material - Mounting Hardware	Stainless Steel Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum

Series	-40 °C
Specifications	Non-Fused <ul style="list-style-type: none">Enclosure Gasket - NeopreneHandle - Valox®Shaft (Unfused) - Valox®Top - Valox®
Style	Replacement Cover
Type	Accessories
UPC	783585763156

Dimensions

Weight	1 lb
--------	------

Certifications And Compliance

Industry Standard(s)	cULus Listed
----------------------	--------------

Product Assets

- [Brochures - Circuit-Lock® Motor Disconnects](#)
- [Catalog Page - WDK F-8 Catalog Page](#)
- [Installation Manuals - HUBBELL 30 AMP CIRCUIT-LOCK DISCONNECT SWITCH | Installation manual](#)
- [Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
- [Sales Drawings - M-14707](#)
- [Specifications - HBLDS30RCP](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)