

Portable Outlet Boxes, Boxes and Plates, Box with Strain Relief, 1-Gang Front and Back Non-Metallic, Furnished with 1) Blank Plate

By Hubbell Wiring Device-Kellems
Catalog # [HBLPOB1](#)



Temporary Power Products, Portable Outlet Boxes, Boxes and Plates, Box with Strain Relief, 1-Gang Front and Back, Yellow Non-Metallic, Furnished with 1) Blank Plate

Features

- Impact resistant Valox® cover plate

Application

Devices and Splices

Performance

- Environmental - Flammability - UL 94V-0, 94-5VA classification
- Environmental - Impact and Crush Resistance - In accordance with UL 514C, UL50, C22.2 No. 18 and C22.2 No. 94.
- Environmental - Moisture Resistance - Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates.Dry, indoors locations, Enclosure Type 1 with all other cover plates
- Environmental - Operating Temperature - 80°C maximum
- -35°C minimum
- Environmental - UV Resistance - All materials are UV stabilized

General

Catalog Number	HBLPOB1
Color	Yellow
Construction	Fabricated
Cord Range	.38" - .75"
EU RoHS Indicator	Yes
Item Type	Weatherproof
Knockouts	1) Hub
Material	Non-Metallic
Material - Mounting Hardware	Cable Mounted
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">• Bonding Strap - Brass• Cord Connector - Nylon nut• Nylon Gotcha® ring• Neoprene grommet• Gasket - UL recognized closed-cell foam• Grounding Screw - Brass

Style	Indoor Screws - Zinc Plated Steel
Type	With One Blank Cover Plate
UPC	Outlet Box 783585318103

Dimensions

Dimensions	5.38 in x 4.2 in x 3.18 in
Display Size	Standard Sized Product
Height	3.18 in
Length	5.38 in
Weight	1 lb
Width	4.2 in

Conductor Related

Cable Entry	Top Hub
-------------	---------

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Industry Standard(s)	<ul style="list-style-type: none">• C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No. 0.4• UL 514C, UL467 and UL50 Enclosures Types 1, 3R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Pallet Quantity	560

Product Assets

[Catalog Page - WDK C-12 Catalog Page](#)
[Catalog Page - WDK H-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBLPOB1 AutoCAD Drawing](#)

[Installation Manuals - WIRING_PD1385_INSTALLINST](#)

[Literature - Safety Product Guide](#)

[Literature - PULP & PAPER SOLUTIONS](#)

[Literature - Pulp & Paper Solutions](#)

[Sales Drawings - WDK_HBLPOB1_DRAWING_PDF](#)

[Specifications - Wiring HBLPOB1 Specification Sheet](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Watertight Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLPOB1-SPEC-EN | REV 7/2025