



Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 3-Phase 120/208V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL560B9W](#)



Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 3-Phase 120/208V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

| | |
|-----------------|------------------------|
| Color | Blue |
| Number Of Poles | 4-Pole |
| Series | Advantage Switch-Rated |
| Style | IP69k NEMA 4X |
| Type | Inlet |
| UPC | 783585479330 |

Electrical Ratings

| | |
|----------------------------|-----------------------|
| Amperage Rating | 60/63 A |
| Current / Amperage Rating | 60/63 A |
| Voltage Rating | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 5-Wire |
|-----------------|--------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Wiring G-6 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - HBL560B9W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL560_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)

Related Products

[HBL560P9W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Watertight](#)
[PC60 - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic](#)
[HBL560B9W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Flanged Inlet, 60A 3-Phase Wye 120/208V AC, Watertight](#)
[BB601W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/4" NPT Hub, Angled, Mounting ScrewsIncluded Cast Aluminum](#)
[BB602W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/2" NPT Hub, Angled, Mounting ScrewsIncluded Cast Aluminum](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL560B9W-SPEC-EN | REV 5/2023