



## Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60/63A 120/208V AC, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems  
Catalog # [HBL560P9W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60/63A  
120/208V AC, NEMA 4X/IP69K

### Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

### General

Color	Blue
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Plugs
UPC	783585479095

### Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

### Conductor Related

Number Of Wires	5-Wire
-----------------	--------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Wiring G-6 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - HBL560P9W AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1303\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Safety Product Guide](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_HBL560P9W\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)

### Related Products

[BB601W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/4" NPT Hub, Angled, Mounting Screws Included Cast Aluminum](#)  
[HBL560P9W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Watertight](#)  
[BB602W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/2" NPT Hub, Angled, Mounting Screws Included Cast Aluminum](#)  
[HBL560R9W - Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60/63A 120/208V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K](#)  
[HBL560B9W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Flanged Inlet, 60A 3-Phase Wye 120/208V AC, Watertight](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBL560P9W-SPEC-EN | REV 5/2023