



## Complete Unit With 20A Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Black/Brass Finish

By Hubbell Wiring Device-Kellems  
Catalog # [PT7FSDBRS3A](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush Duplex Series, Complete Unit With 20A Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Black/Brass Finish

### Features

- Complete 3" Fire-Rated Poke-Through
- Prewired 20A Duplex Receptacle
- (2) 1/2" Diameter Holes for Low Voltage Wiring
- Non-metallic Cover with Brass Flange
- Includes Junction Box

### General

Application - For Use On	Carpet
EU RoHS Indicator	No
Finish Type	Black/Brass
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Style	FRPT - Complete Kits
UPC	783585494173



### Certifications and Compliance

- |                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• cULus Listed</li><li>• Meets ADA Standards</li><li>• UL 514A Listed</li></ul> |
|----------------------|---|

### Product Assets

[Catalog Page - Wiring Q-32 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Engineering Drawing - PT7FSDBRS3A AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1962\\_INSTALLINST](#)  
[Literature - Delivery Systems Product Guide](#)  
[Sales Drawings - WDK\\_PT7FSDB\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

### Related Products

[FRFGYA - Flush Duplex Series, Flush Service Fitting, Gray](#)  
[FRFBLA - Flush Duplex Series, Flush Service Fitting, Black](#)  
[FRFBRS2A - Flush Duplex Series, Flush Service Fitting, Brass](#)  
[FRFBRA - Flush Duplex Series, Flush Service Fitting, Brass](#)  
[FRFIA - Flush Duplex Series, Flush Service Fitting, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PT7FSDBRS3A-SPEC-EN | REV 5/2023