



Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [PT7IGFSDIA](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush Duplex Series, Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Ivory

Features

- Complete 3" Fire-Rated Poke-Through
- Prewired 20A IG Duplex Receptacle
- (2) 1/2" Diameter Holes for Low Voltage Wiring
- Non-metallic Cover with Painted Aluminum Flange
- Includes Junction Box

General

Application - For Use On	Carpet
EU RoHS Indicator	No
Finish Type	Ivory
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex IG Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Style	FRPT - Complete Kits
UPC	783585494210



Certifications and Compliance

- | | |
|----------------------|-----------------------|
| Industry Standard(s) | • cULus Listed |
| | • Meets ADA Standards |
| | • UL 514A Listed |

Product Assets

[Catalog Page - Wiring Q-32 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - PT7IGFSDIA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1962_INSTALLINST](#)
[Literature - Delivery Systems Product Guide](#)
[Sales Drawings - WDK_PT7IGFSD_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[FRFBRS2A - Flush Duplex Series, Flush Service Fitting, Brass](#)
[FRFBLA - Flush Duplex Series, Flush Service Fitting, Black](#)
[FRFGYA - Flush Duplex Series, Flush Service Fitting, Gray](#)
[FRFIA - Flush Duplex Series, Flush Service Fitting, Ivory](#)
[FRFBRA - Flush Duplex Series, Flush Service Fitting, Brass](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PT7IGFSDIA-SPEC-EN | REV 5/2023