



Recessed 6" Series, Kit

By Hubbell Wiring Device-Kellems
Catalog # [S1R6PTDEHGRY](#)

Fire Rated Poke Throughs, Recessed 6" Series, Kit, (1)
S1R6PTFIT, (1) S1R6SPD, (1) S1R6SPE, (1) S1R6SPH, (1)
S1R6CVRGRY



Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

General

Accessory Type	6" FRPT Kit
Application - For Use On	Concrete
Color	Gray
Construction	Fabricated
Construction Material - Main	6 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	Gray Powder Coat Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	6" Core Hole
Number Of Outlets	(2) 50% Left Side Sub Plates- (3) iSTATION Opening, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Right Side- (4) 20A Pre- Wired Receptacles, 1 or 2 Circuits, 18" Leads
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	6" Recessed Rated Poke Through Kit
UPC	783585590042

Conductor Related

Cable Entry Through Cover

Certifications and Compliance

- Industry Standard(s)
- cULus Listed
 - Meets ADA Standards
 - UL 514A Listed

Product Assets

[BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-SIR6](#)
[Catalog Page - WDK P-17 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - 6 INCH RECESSED FRPT AutoCAD Drawing](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Sales Drawings - M12042](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[S1R6DIV - Recessed 6" Series, Replacement Divider](#)
[S1R6SPEXT - Recessed 6" Series, Sub Plate, 1.5" Extension Kit](#)
[S1FRPTJB2 - SystemOne, Fire-Rated Poke-Throughs, 4-11/16" Junction Box](#)
[S1R6PPPT - Recessed 6" Series, Pre-Pour Tube](#)
[S1FRPTJB - SystemOne Accessories, Junction Box](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-S1R6PTDEHGRY-SPEC-EN | REV 1/2024