

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic

By Hubbell Wiring Device-Kellems  
Catalog # [PC60](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 60A All Wire, Gray Non-Metallic

Features

- Cap assemblies provide watertight sealing
- Manufactured with non-metallic material

Application

- All 60 and 63 Amp

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 classification
- Environmental - Moisture Resistance - IP67 Suitability
- Environmental - Operating Temperatures - Max. Continuous:75°C
- Min. Continuous:-40°C w/o impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Ratings are a part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

General

Catalog Number	PC60
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Plug Cover
Material	Composite
Material - Mounting Hardware	Cord Mounted
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Accessories
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Stainless Steel</li><li>• Gaskets - Neoprene</li></ul>



Style	Hinge Spring - Stainless Steel
Type	Replacement Part - Plug Cover
UPC	Fits all 60 and 63A Closure Caps 783585373607

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Connectivity	Pressure Terminal Screws
--------------	--------------------------

Conductor Related

Cord Type	All Portable
-----------	--------------

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	810

Product Assets

[Catalog Page - WDK G-11 Catalog Page](#)  
[Catalog Page - WDK G-29 Catalog Page](#)  
[Catalog Page - WDK G-6 Catalog Page](#)  
[Catalog Page - WDK G-7 Catalog Page](#)  
[Catalog Page - WDK AA-24 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - PC60 AutoCAD Drawing](#)  
[Engineering Drawing - M7241\\_ACAD](#)  
[Installation Manuals - WIRING\\_PD1311\\_INSTALLINST](#)  
[Literature - IEC Pin & Sleeve Devices](#)

Literature - Hubbell PRO Pin & Sleeve Brochure  
Literature - PULP & PAPER SOLUTIONS  
Literature - Pulp & Paper Solutions  
Literature - Hubbell Marine Full Line Catalog

Sales Drawings - WDK\_PC60\_DRAWING\_PDF  
Sales Drawings - M7241  
Specifications - Wiring PC60 Specification Sheet  
Warranty - Industrial & Commercial Products



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
WDK-PC60-SPEC-EN | REV 4/2025