



RCPT DUP,15A 125V,8-HOLE QCK-PLT,IV

By Hubbell Wiring Device-Kellems
Catalog # [RR15EQI](#)

RCPT DUP,15A 125V,8-HOLE QCK-PLT,IV



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

General

Color	Ivory
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778301063

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - RR15EQI AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2451_INSTALLINST](#)
[Sales Drawings - WDK_RR15EQ_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RR15LA - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Duplex, 15A125V, 2-Pole 3-Wire Grounding, 5-15R, Push Terminals, Light Almond](#)
[RR15I - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Duplex, 15A125V, 2-Pole 3-Wire Grounding, 5-15R, Push Terminals, Ivory](#)
[RR15QITR - TradeSelect, Straight Blade Receptacles, Residential Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 8 Hole Push-In Wiring, Light Almond](#)
[RR15BK - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Duplex, 15A125V, 2-Pole 3-Wire Grounding, 5-15R, Push Terminals, Black](#)
[SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RR15EQI-SPEC-EN | REV 5/2023