

# TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [RR201IWRTR](#)

TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory



## General

Application	Residential Receptacles
Catalog Number	RR201IWRTR
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94 V-1  Environmental - Operating temperature - -20°C to 60°C, without impact  Mechanical - Product Identification - Ratings are a permanent part of the device  Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA C22.2, No. 41
UPC	883778302961

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 41 File No. 23253  NEMA® WD-6 Compliant  UL Listed to UL498 File No. E2185
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK Z-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - RR201IWRTR AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2131\\_INSTALLINST](#)  
[Literature - Residential Catalog](#)  
[Literature - Residential Product Guide](#)  
[Sales Drawings - WDK\\_RR201WRTR\\_DRAWING\\_PDF](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)  
[Video - Tamper-Resistant Receptacles](#)  
[Video - Tradeselect Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-RR2011WRTR-SPEC-EN | REV 6/2024