



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Brown

By Hubbell Wiring Device-Kellems
Catalog # [RRD155](#)



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Brown

Application

Residential Receptacles

General

Color	<ul style="list-style-type: none">BrownBrun
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778300660

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	3750

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	6-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring AA-5 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - RRD155 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2282_INSTALLINST](#)
[Sales Drawings - WDK_RRD155_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tradeselect Devices](#)

Related Products

[P26 - Wallplate, 1-Gang, 1\) Decorator, Brown](#)
[RRD15E - RESI DUP DEC RCPT 15A 125V 8 HOLE BR](#)
[RRD201 - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown](#)
[RRD15S - TradeSelect, Straight Blade, DecoratorDuplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)
[RRD15 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RRD155-SPEC-EN | REV 5/2023