

# SNAPConnect® Heavy Duty Hospital Grade AUTOGUARD® Self- Test GFCI Receptacle, 20A, White

By Hubbell Wiring Device-Kellems

Catalog # [SNAPGF83W](#)

SNAPConnect® Straight Blade GFCI Receptacle, 20A,  
Commercial Hospital Grade, Self-Test, 125V, 2-Pole 3-Wire  
Grounding, 5-20R.



## Features

- Audible SNAP indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Triple wipe construction
- Protects against line and load reversal, no power to the face or downstream if device is miswired

## General

|                |                             |
|----------------|-----------------------------|
| Application    | Commercial Hospital Grade   |
| Catalog Number | SNAPGF83W                   |
| Color          | White                       |
| Item Type      | Self test GFCI receptacle   |
| Material       | Nylon                       |
| Series         | Hospital Grade              |
| Size           | 4.12 in x 1.75 in x 1.48 in |
| Type           | Standard                    |
|                | Standard                    |
| UPC            | 783585746555                |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 1.48 in x 1.75 in x 4.12 in |
| Height     | 4.12 in                     |
| Length     | 1.48 in                     |
| Width      | 1.75 in                     |

## Electrical Ratings

|                           |              |
|---------------------------|--------------|
| Current / Amperage Rating | 20 A         |
| Phase                     | Single Phase |
| Voltage Rating            | 125 VAC      |
| Wattage                   | 2500 W       |

## Conductor Related

|           |             |
|-----------|-------------|
| Wire Size | SNAPConnect |
|-----------|-------------|

## Certifications And Compliance

|                      |  |
|----------------------|--|
| Industry Standard(s) | UL 943 and Meets All NEC® Requirements |
| Nema Rating          | 5-20R                                  |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK L-15](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK X-15](#) [Catalog Page - WDK K-6](#) [Catalog Page - WDK Catalog Full 2024](#) [Engineering Drawing - M14625\\_ACAD](#) [Installation Manuals - PD2986](#) [Literature - Hospital Grade GFCI Receptacles](#) [Sales Drawings - M14625](#) [Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-SNAPGF83W-SPEC-EN | REV 6/2024