

Kellems Wire Management, Splicing Grips, Non-rotating Wire Rope Splicing, 1.00-1.13"



By Hubbell Wiring Device-Kellems
Catalog # 03316003

Kellems Wire Management, Splicing Grips, Non-rotating Wire Rope Splicing, 1.00-1.13"

Features

- Galvanized steel meshes constructed in triple, double and single weave
- Non-rotating barrel

Application

Wire Rope Splicing

Performance

- Mechanical - Approximate Breaking Strength - 16,000 (71,168)
- Mechanical - Approximate Strength of Grip per Foot - 7.00 (2.13)
- Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength)

General

Approx Breaking Strength	16,000 lbs
Catalog Number	03316003
EU RoHS Indicator	Yes
Environmental Conditions	No Limitations
Material	Steel, Galvanized
Material - Mounting Hardware	On Cable Ends
Series	Wire Rope Grips
Specifications	- Fastener - Plastic - Strand - Galvanized Steel - Strand Tabs - Copper - Tag - Mylar
Style	Closed Mesh, Triple, Double, Single Weave
Type	Regular Wire Rope
UPC	783585317182

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Conductor Related

Cable Diameter Range	1.00 in-1.13 in
Cable Size	1.00"-1.13" (2.54-2.86)
Number of Conductors	1

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog Page - WDK W-14 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_30920103_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Sales Drawings - WDK_03316003_DRAWING_PDF](#)
[Specifications - 3316003 Specification Sheet French](#)
[Specifications - 03316003 Specification Sheet](#)
[Specifications - Wiring 03316003 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)

