

2-Gang AFB Series, Cover  
Assembly, Bronze Powder Paint  
Finish

By Hubbell Wiring Device-Kellems  
Catalog # [2GAFBCVRBRZ](#)



Raised Access or Wooden Floors, Recessed, 2-Gang AFB Series,  
Cover Assembly, Bronze Powder Paint Finish

Features

- Surface Style without Cover Insert
- 180 Degree Cover Opening to Lay Flat and Reduce Tripping Hazards
- Two Large Cable Egress Doors
- Die Cast Aluminum Cover Construction for Enhanced Durability
- Meets UL 514A Scrub Water Requirements
- ADA Compliant

Application

For Use with Raised Access Floor Boxes

General

Application - For Use On	Raised Access; Wood
Catalog Number	2GAFBCVRBRZ
Color	Bronze Powder Coat
Construction	Cast Aluminum
Cover Shape	Rectangle
EU RoHS Indicator	Contact Manufacturer
Material	Cast Aluminum
Mounting Method	Mounts to Box
Mounting Type	(4) Screw Mount
Number of Gang(s)	2-Gang
Series	<ul style="list-style-type: none"><li>• Recessed Rectangular - AFB Series</li><li>• Recessed - AFB Series</li></ul>
Size	2-Gang
Type	Recessed Access Floor Box Cover
Type of Use	Carpet/Surface

Typical Application	Carpet/Surface
UPC	783585526874

Dimensions

Length	15 in
Width	8.75 in

Conductor Related

Cable Entry	(2) Egress Doors
-------------	------------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• cULus</li><li>• UL514</li></ul>
----------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Floorbox Selection Guide](#)  
[Catalog Page - WDK O-48 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - 2GAFBCVRBRZ AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2624\\_INSTALLINST](#)  
[Literature - Connexion 2.0 Zone Distribution System](#)  
[Literature - Hubbell SystemOne Recessed Floor Boxes](#)  
[Sales Drawings - WDK\\_2GAFBCVR\\_DRAWING\\_PDF](#)  
[Specifications - 2GAFBCVRBRZ Specification Sheet French](#)  
[Specifications - 2GAFBCVRBRZ Specification Sheet](#)  
[Specifications - Wiring 2GAFBCVRBRZ Specification Sheet](#)  
[Warranty - Industrial & Commercial Products](#)

