

2-Gang AFB Series, 5.50" Deep
Rectangular Box with Installation
Cover, No Knockouts, Chicago
Approved

By Hubbell Wiring Device-Kellems
Catalog # [AFB2G50CHI](#)



Raised Access or Wood Floorboxes, Galvanized Stamped Steel Box, Recessed, 2-Gang AFB Series, 5.50" Deep Rectangular Box with Installation Cover, No Knockouts, Chicago Approved

Features

- Chicago Approved Recessed 2-Gang Rectangular Floorbox
- For Use In Raised Access or Wood Floors
- Mounts in Floors ¾" to 2" thick
- Box Includes Installation Cover
- Each Gang Includes (1) 6" Solid Conductor Grounding Pigtail
- Plates Available

Application

For Use in Raised Access or Wooden Floors

General

Application - For Use On	Raised Access; Wood
Catalog Number	AFB2G50CHI
Construction	Folded
Construction Material - Main	Steel
Cover Shape	Rectangle
EU RoHS Indicator	Contact Manufacturer
Material	Pre Galvanized Steel
Mounting Method	Drop-Into Floor
Mounting Type	Mechanical Mount
Number of Gang(s)	2-Gang
Series	<ul style="list-style-type: none">• Recessed Rectangular - AFB Series• Recessed - AFB Series
Size	Standard Sized Product
Sub Brand	Raised Access Floor Boxes
Type	Recessed Access Floor Box
UPC	783585447216

Dimensions

Dimensions	6.62 in x 12.67 in x 5.06 in
Height	5.06 in
Length	6.62 in
Width	12.67 in

Conductor Related

Cable Entry	Through Cover
-------------	---------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus• UL514
----------------------	---

Product Assets

- [BIM - Electrical_Equipment-Floor_Box-Hubbell_Wiring-2_Gang_AFB_Deep-AFB2G50CHI](#)
- [BIM - Electrical_Equipment-Floor_Box-Hubbell_Wiring-2_Gang_AFB_Deep-AFB2G50](#)
- [Brochures - Floorbox Selection Guide](#)
- [Catalog Page - WDK O-48 Catalog Page](#)
- [Catalog Page - WDK O-46 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - AFB2G50CHI AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2612_INSTALLINST](#)
- [Literature - Connexion 2.0 Zone Distribution System](#)
- [Literature - Hubbell SystemOne Recessed Floor Boxes](#)
- [Sales Drawings - WDK_AFB2G50CHI_DRAWING_PDF](#)
- [Specifications - AFB2G50CHI Specification Sheet French](#)
- [Specifications - AFB2G50CHI Specification Sheet](#)
- [Specifications - Wiring AFB2G50CHI Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)