

SNAPConnect® Heavy Duty Hospital Grade Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW82LA](#)



Straight Blade SNAPConnect® Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self-Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R.

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

| | |
|--------------------------|-------------------------------------|
| Application | Commercial Hospital Grade |
| Catalog Number | SNAPGFTW82LA |
| Color | Light Almond |
| Environmental Conditions | Weather Resistant |
| Item Type | Self test GFCI receptacle |
| Material | Nylon |
| Series | Hospital Grade |
| Size | 4.12 in x 1.75 in x 1.48 in |
| Type | Tamper-Resistant, Weather Resistant |
| | Tamper-Resistant, Weather Resistant |
| UPC | 783585746241 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 1.48 in x 1.75 in x 4.12 in |
| Height | 4.12 in |
| Length | 1.48 in |
| Width | 1.75 in |

Electrical Ratings

| | |
|---------------------------|--------------|
| Current / Amperage Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------|-------------|
| Wire Size | SNAPConnect |
|-----------|-------------|

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | UL 943 and Meets All NEC® Requirements |
| Nema Rating | 5-15R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK K-7](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK L-14](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#) [Engineering Drawing - M14625_ACAD](#) [Installation Manuals - PD2986](#) [Sales Drawings - M14625](#) [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-SNAPGFTW82LA-SPEC-EN | REV 6/2024