

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/4" NPT Hub, Angled, Mounting Screws Included Aluminium moulé

Par Hubbell Wiring Device-Kellems
No de catalogue [BB601W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessory, Back Box, For 60A 1 1/4" NPT Hub, Angled, Mounting Screws Included, Gray Cast Aluminum.



Performance

Environmental - Moisture Resistance - IP67 Suitability

Général

Numéro de catalogue	BB601W
Couleur	<ul style="list-style-type: none">AluminiumAluminium
La construction	Cast
Indicateur RoHS de l'UE	Oui
Type d'article	Boîte de montage
Les Knockouts	1 1/4" NPT Moyeu
Matériau	Aluminium
Matériau - Matériel de montage	Vis de montage
Nombre de prises	Accepte 1 appareil
Série	Boîtes d'encastrement et adaptateurs
Style	15 Degré
Plage de température	Limité par l'appareil
Type	Boîte arrière
CUP	783585390758

Dimensions

Taille de l'affichage	Pour les appareils de 60 et 63 ampères
-----------------------	--

Chef d'orchestre

Entrée par câble	Par le biais du Hub
------------------	---------------------

Certifications et conformité

Norme(s) industrielle(s)	Test d'étanchéité à la pluie et de givrage externe UL
Normes - Conformité à la directive RoHS	CM

Logistique

Quantité de cartons	1
Quantité de palettes	186

Documentation

[Catalogues - WDK Catalog Full 2024](#)
[Dessins de vente - WDK_BB601W_DRAWING_PDF](#)
[Garantie - Industrial & Commercial Products](#)
[Littérature - Dual-Certified IEC Pin & Sleeve Devices](#)
[Littérature - Hubbell Marine Full Line Catalog](#)
[Littérature - IEC Pin & Sleeve Devices](#)
[Littérature - Hubbell PRO Pin & Sleeve Brochure](#)
[Littérature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
[Page du catalogue - WDK H-13 Catalog Page](#)
[Page du catalogue - WDK G-11 Catalog Page](#)
[Page du catalogue - WDK G-35 Catalog Page](#)
[Page du catalogue - WDK AA-24 Catalog Page](#)
[Page du catalogue - WDK G-28 Catalog Page](#)
[Spécifications - BB601W](#)
[Spécifications - BB601W](#)
[Spécifications - Wiring BB601W Specification Sheet](#)

