

Kellems Wire Management, Cord  
Connectors, Straight Female .88-  
1.0", 1", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [FHC1043](#)

Kellems Wire Management, Cord Connectors, Straight Female  
.88-1.0", 1", Aluminum

Features

- Machined aluminum straight female connector

Application

Straight Female- Form 4

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	FHC1043
Color Code	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Inches (mm) - .88"-1.00" (22.2-25.4)</li><li>• Form Size - F4</li><li>• Material - Aluminum</li><li>• NPT Hub Size - 1 Inch</li></ul>
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Female



UPC783585203430

Dimensions

Display Size	1" NPT
Hub Size	1"

Conductor Related

Conductor Range	0.88-1 in (22.2-25.4 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK W-72 Catalog Page](#)
- [Catalog Page - WDK W-73 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Specifications - Wiring FHC1043 Specification Sheet](#)
- [Specifications - FHC1043 Specification Sheet French](#)
- [Specifications - FHC1043 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)