

**HUBBELL**  
Wiring Device-Kellems

## **GFP1305**

By Hubbell Wiring Device-Kellems  
Catalog # [GFP1305](#)

Power Protection Products, GFCI High Amperage Portables,  
Industrial/Commercial, Manual Set, 30A 120V AC, 6' Cord  
Length, 4-6 mA Trip Level, Black.



## Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Mécanisme de verrouillage électromagnétique
- Déclenchement en cas de contact de terre et neutre au côté de la charge
- Lumière clignotante rouge et alarme sonore facultative
- Protection neutre ouverte
- Déclenche en cas de perte de neutre

## General

Application	Line Cord Only No Devices
Catalog Number	GFP1305
Color	
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
Performance	Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure Electrical - Operating Voltage Range - 85% to 110% Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency Environmental - Construction - Industrial grade design Environmental - Housing Rating - UL Type 4X Environmental - Leakage Current - At 93% Humidity leakage current is zero Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F. Environmental - Type - Meets UL943 Class A GFCI
Series	Extra Heavy Duty
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Straight Blade
UPC	783585005645

## Dimensions

Outside Diameter	0.335
Weight	3.9 lb

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

## Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD1827\\_INSTALLINST](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_GFP13\\_DRAWINGS\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-GFP1305-SPEC-EN | REV 6/2024