



Kellems Wire Management, Dusttight Grips, Strain Relief, .54-.73", 3/4" Insulated

By Hubbell Wiring Device-Kellems
Catalog # [073031209A](#)



Kellems Wire Management, Dusttight Grips, Strain Relief,
.54-.73", 3/4" Insulated

Features

- Aluminum Fitting
- Galvanized steel mesh provides high strength

Application

Light Duty

General

Construction	Woven
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)• Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Series	Dust-Tight
Style	For Insulated Cables
Thread Size	3/4" NPT
Type	Insulated, Wide Range
UPC	783585550176

Dimensions

Display Size 3/4" NPT

Conductor Related

Cable Diameter Range 0.54 in-0.73 in
Cable Size .54"-.73" (1.37-1.85)

Certifications and Compliance

Industry Standard(s)

- CSA Certified
- UL Listed

Logistics

Carton Quantity 20

Product Assets

[Catalog Page - Wiring X-55 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)

Related Products

[07401017 - Kellems Wire Management, Deluxe Cord Grips, Straight Male, .500-.625", 3/4" with Mesh](#)
[07401013 - Kellems Wire Management, Deluxe Cord Grips, Straight Male, .250-.375", 3/4" with Mesh](#)
[091041005 - Kellems Wire Management, Adapters for Multi-Pin Connectors, 7/8" X 20", Aluminum](#)
[07401015 - Kellems Wire Management, Deluxe Cord Grips, Straight Male, .375-.500", 3/4" with Mesh](#)
[07401018 - Kellems Wire Management, Deluxe Cord Grips, Straight Male, .625-.750", 3/4" with Mesh](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK_073031209A_SPEC | REV 3/2023