

Kellems Wire Pulling Grips,
Underground Rotating Eye, 2.50-
2.99 in, Standard

By Hubbell Wiring Device-Kellems
Catalog # 03301028

Kellems Wire Management, Pulling Grips, Underground Rotating
Eye, 2.50-2.99", Standard

Features

- Rotating eye for spin out of pulling torque after load release
- The multiweave styles available add strength for big pulling jobs
- The galvanized steel mess grip provides strength for secure pulling

Application

Underground Pulling

Performance

- Mechanical - Approximate Breaking Strength - 33,000 (146,784) Lbs. (N)
- Mechanical - Cable Diameter Range - 2.50"-2.99" (6.35-7.59)
- Mechanical - Working Load - 6600 (29356.8) Lbs. (N)

General

Approx Breaking Strength	33,000 lbs
Catalog Number	03301028
Color	Metallic
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	6600
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Series	Underground K-Type
Specifications	• Bushing - Steel • Eye - Steel • Lug - Steel • Shoulders - Aluminum • Strand - Galvanized Steel • Tag - Mylar
Style	Closed Mesh, Double Weave
Type	Rotating Eye, Standard Length
UPC	783585314327



Working Load Limit6,600 lb

Dimensions

Weight6.5 lb

Conductor Related

Cable Diameter Range	2.50 in - 2.99 in
Cable Diameter Range Metric	6.35 cm - 7.59 cm
Cable Size	2.50"-2.99" (6.35-7.59)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)CSA Certified

Logistics

Carton Quantity	2
Pallet Quantity	36

Product Assets

[Catalog Page - WDK W-9 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_D5722301_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Sales Drawings - WDK_03301028_DRAWING_PDF](#)
[Specifications - 03301028 Specification Sheet](#)
[Specifications - Wiring 03301028 Specification Sheet](#)
[Specifications - 3301028 Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)