



Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [H125](#)



Kellems Wire Management, Liquidtight System, Straight Male
Liquid Tight Connector, 1 1/4", Steel, Non-Insulated.

Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

General

| | |
|-------------|--|
| Material | Iron, Zinc Plated |
| Performance | <ul style="list-style-type: none">• Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)• Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B) |
| Style | Straight |
| Type | <ul style="list-style-type: none">• Metallic Liquidtight Fittings• Metallic Liquidtight Fittings |
| UPC | 783585034058 |

Dimensions

| | |
|---------------------------------|-------------------|
| Dimension - L Length Overall mm | 2.031 in |
| Dimension - Thread Size | 1-1/4"-11-1/2 NPT |
| Dimension - Width mm | 2.187 in |
| Trade Size | 1 1/4 |

Certifications and Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• CSA Certified• UL 514B |
|----------------------|---|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

[Catalog Page - WDK W-91 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - H125 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1857_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Sales Drawings - WDK_H125_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)

Related Products

[074093405 - Kellems Wire Management, Liquidtight System, Straight, 1 1/4", Non-Insulated with Mesh](#)
[H125CNK - Kellems Wire Management, Liquidtight System, Straight Male Type A Connector, 1 1/4", Steel](#)
[G1125 - Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-H125-SPEC-EN | REV 1/2024