



# Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated

By Hubbell Wiring Device-Kellems  
Catalog # [H1259](#)



Kellems Wire Management, Liquidtight System, 90 Degree  
Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated.

## Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

## Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

## General

Material	Iron, Zinc Plated
Performance	<ul style="list-style-type: none"><li>• Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)</li><li>• Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B)</li></ul>
Style	90°
Type	<ul style="list-style-type: none"><li>• Metallic Liquidtight Fittings</li><li>• Metallic Liquidtight Fittings</li></ul>
UPC	783585034256

## Dimensions

Dimension - Thread Size	1-1/4"-11-1/2 NPT
Dimension - Width mm	2.187 in
Trade Size	1 1/4

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL 514B</li></ul>
----------------------	---

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalog Page - WDK W-91 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - H1259 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1857\\_INSTALLINST](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Sales Drawings - WDK\\_H1259\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Kellems Wire Management Solutions](#)

## Related Products

[G1125 - Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet](#)  
[074093425 - Kellems Wire Management, Liquidtight System, 90 Degree, 1 1/4", Non-Insulated with Mesh](#)  
[H1259CNK - Kellems Wire Management, Liquidtight System, 90 Male Type A Connector, 1 1/4", Steel](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-H1259-SPEC-EN | REV 1/2024