

# EdgeConnect™ Twist-Lock® Receptacle with Spring Termination, 20A, 125V, L5, 20R, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2310ST](#)

20A, 125V EdgeConnect™ Twist-Lock® Receptacle with Spring Termination.



## Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

## General

Application	
Catalog Number	HBL2310ST
Color	
Environmental Conditions	
Insulation	N/A
Item Type	Single Receptacle
Material	Nylon
Mounting Type	
Number Of Poles	2
Size	Standard Sized Product
Temperature Rating	Maximum continu 75°C ; Minimum -40°C (sans impact)
UPC	783585569543

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V Minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3
Wire Size	14 AWG - 10 AWG solid, 14 AWG - 8 AWG stranded (including compact stranded)

## Certifications And Compliance

Industry Standard(s)	UL Listed To UL 498 CSA Certified to Specification C22.2 No. 42
Nema Rating	L5-20R

## Logistics

Carton Quantity	30
Pallet Quantity	3060

## Product Assets

[3D Product View - Twist-Lock® EdgeConnect HBL2320ST](#)  
[Receptacle AR Model](#)  
[Brochures - EdgeConnect Brochure](#)  
[Brochures - Twist-Lock Edge Series French](#)  
[Brochures - Twist-Lock Edge Series](#)  
[Brochures - EdgeConnect Brochure French](#)  
[Catalog Page - WDK B-35 Catalog Page](#)  
[Catalog Page - WDK B-27 Catalog Page](#)  
[Catalog Page - WDK B-23 Catalog Page](#)  
[Catalog Page - WDK B-33 Catalog Page](#)  
[Catalog Page - WDK B-31 Catalog Page](#)  
[Catalog Page - WDK B-21 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M13891\\_ACAD](#)  
[Installation Manuals - PD2880](#)  
[Literature - Healthcare Product Solutions](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)  
[Literature - EdgeConnect™ Technology](#)  
[Literature - Twist-Lock® Edge Series Devices](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Sales Drawings - M13891](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Twist-Lock® Edge Plugs and Inlets](#)  
[Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)  
[Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-HBL2310ST-SPEC-EN | REV 6/2024