



CFB2G & CFB4G Rectangular Series, Surface Cover Assembly, Aluminum Powder Paint Finish

By Hubbell Wiring Device-Kellems
Catalog # [24GCCVRALU](#)



SystemOne Recessed Floor Box Cover, 2 and 4-Gang, For Concrete Floors, Aluminum Powder Finish.

Features

- Surface Style without Cover Insert
- 180 Degree Cover Opening to Lay Flat and Reduce Tripping Hazards
- Two Large Cable Egress Doors
- Die Cast Aluminum Cover Construction for Enhanced Durability
- Meets UL 514A Scrub Water Requirements
- ADA Compliant
- 180 degree cover opening to lay flat and reduce tripping hazards
- Two large cable egress doors
- Die cast aluminum cover construction for enhanced durability

Application

For Use with Concrete Floor Boxes

General

Application - For Use On	Concrete
Color	<ul style="list-style-type: none"> • Aluminum Powder Coat • Aluminium
Construction	Cast Aluminum
Cover Shape	Rectangle
Cover Type	Rectangle
EU RoHS Indicator	Contact Manufacturer
Finish Type	Aluminium
Material	Cast Aluminum
Mounting Method	Mounts to Box
Mounting Type	(4) Screw Mount
Number of Gang(s)	2-Gang
Series	Recessed - CFB Series
Size	2-Gang;4-Gang
Type	<ul style="list-style-type: none"> • Recessed Concrete Floor Box Cover • Recessed Concrete Floor Box Cover
Type of Use	Carpet/Surface
Typical Application	Carpet/Surface
UPC	783585446431

Dimensions

Length	11.69 in
Width	7.19 in

Conductor Related

Cable Entry	(2) Egress Doors
-------------	------------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • cULus • UL514
----------------------	--

Product Assets

- [Catalog Page - WDK O-6 Catalog Page](#)
- [Catalog Page - WDK O-7 Catalog Page](#)
- [Catalog Page - WDK O-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - 24GCCVRALU AutoCAD Drawing](#)
- [Engineering Drawing - 2G RECESSED FLOOR BOX Drawing](#)
- [Engineering Drawing - 4 Gang Recessed Floor Box Drawing](#)
- [Installation Manuals - WIRING_PD2624_INSTALLINST](#)
- [Literature - Delivery Systems Product Guide](#)
- [Literature - Hubbell SystemOne Recessed Floor Boxes](#)
- [Literature - SystemOne Eternal™ Series 4-Gang PVC Recessed Floor Boxes \(EP-WDK-SF-EN-01478\)](#)
- [Literature - SystemOne Eternal™ Series 4-Gang Recessed Floor Boxes \(EP-WDK-SF-EN-01477\)](#)
- [Literature - SystemOne Eternal™ Series 2-Gang Recessed Floor Boxes \(EP-WDK-SF-EN-01473\)](#)
- [Sales Drawings - WDK_CFB2G_DRAWING_PDF](#)
- [Sales Drawings - WDK_CFB4G_DRAWING_PDF](#)
- [Sales Drawings - WDK_24GCCVR_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SystemOne Recessed Floor Boxes](#)

Related Products

[CFB4G30CI - 4-Gang CFB Series Box for Rectangular Covers, 3.25" Minimum Depth of Pour](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-24GCCVRALU-SPEC-EN | REV 1/2024