

Recessed 4" Series, Cast Aluminum  
Box with Brushed Brass Plated  
Cover

By Hubbell Wiring Device-Kellems  
Catalog # [AFBS1R4BRS](#)

Raised Access or Wood Floorboxes, Recessed 4" Series, Cast  
Aluminum Box with Brushed Brass Plated Cover

Features

- Recessed 4" Round Floorbox
- For Use In Raised Access or Wood Floors
- Mounts in Floors 1.00" to 2.50" thick
- Kit includes (1) AFBS1R4BASE Box, (1) AFBS1R4CVRBRS Cover

Application

For Use with Raised Access Floor Boxes

General

Application - For Use On	Raised Access; Wood
Catalog Number	AFBS1R4BRS
Color	<ul style="list-style-type: none"><li>• Cover</li><li>• Brass Finish</li></ul>
Construction	Fabricated
Cover Shape	Round
EU RoHS Indicator	Contact Manufacturer
Finish Type	Brass
Knockouts	4) 1/2", 1) 1/2" - 1"
Material	Composite
Mounting Method	Drop-Into Floor
Mounting Type	Mechanical Mount
Series	Recessed Round - AFB Series
Size	4 Inch Round
Type	Recessed Access Floor Box and Cover
UPC	783585545257

Dimensions



Height5.65 in

Conductor Related

Cable Entry(2) Egress Doors

Certifications And Compliance

Industry Standard(s)

- cULus
- UL514

Logistics

Carton Quantity1  
Pallet Quantity195

Product Assets

[BIM - Electrical\\_Equipment-Floor\\_Box-Hubbell\\_Wiring-AFBS1R4](#)  
[Brochures - Floorbox Selection Guide](#)  
[Catalog Page - WDK O-53 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Customer Notices - Prop 65 Notice](#)  
[Engineering Drawing - AFBS1R4BRS AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2680\\_PD2681\\_INSTALLINST](#)  
[Literature - Hubbell SystemOne 4-Inch Recessed Floor Box for Raised Access and Wood Floors](#)  
[Sales Drawings - WDK\\_AFBS1R4\\_DRAWING\\_PDF](#)  
[Specifications - AFBS1R4BRS Specification Sheet](#)  
[Specifications - Wiring AFBS1R4BRS Specification Sheet](#)  
[Specifications - AFBS1R4BRS Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)

